

**KTB GP 916115 CD S4**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Similar to illustration**



Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Flange plates**

Flange plates in two thicknesses, for easy replacement of pre-assembl

**General ordering data**

Version	Klippon TB (Terminal Box), flange plate, straight, Height: 421 mm, Width: 117 mm, Depth: 3 mm, Gland plates: left, right, Material: Stainless steel 1.4404, electropolished, silver
Order No.	<a href="#">1281280000</a>
Type	KTB GP 916115 CD S4
GTIN (EAN)	4050118071917
Qty.	1 Stück

Erstellungs-Datum May 30, 2023 11:42:13 AM CEST

## KTB GP 916115 CD S4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	421 mm	Height (inches)	16.575 inch
Width	117 mm	Width (inches)	4.606 inch
Net weight	1,120 g		

### General information

Gland plates	left, right	Integral fixing	Screwed
Material	Stainless steel 1.4404	Material thickness	3 mm
Protection class (UL)	Type 3, Type 4X, Type 12	Surface finish	electropolished

### General information on accessories

Material	Stainless steel 1.4404	Material thickness	3 mm
Surface finish	electropolished		

### Classifications

ETIM 6.0	EC000211	ETIM 7.0	EC000211
ETIM 8.0	EC000211	ECLASS 9.0	27-14-24-21
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-14-24-21
ECLASS 11.0	27-14-24-21	ECLASS 12.0	27-14-24-21

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>