

IE-CD-V14MHYB-Y-MA**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Y-distributor, FreeCon version for push-pull plug connector var. 14 as per IEC 61076-3-117 in metal with hybrid 10-pole insert

General ordering data

Version	Y-distributor, FreeCon, Hybrid, IP65
Order No.	1312580000
Type	IE-CD-V14MHYB-Y-MA
GTIN (EAN)	4050118115208
Qty.	1 pc(s).

Creation date March 7, 2023 8:34:21 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-CD-V14MHYB-Y-MA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	715 g
------------	-------

Temperatures

Operating temperature	-40 °C...70 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	70 °C		

General data

Colour	silver	Housing main material	Aluminium profile, Cover: die-cast zinc, painted
Protection degree	IP65	Type of mounting	Screw mounting
UL 94 flammability rating	V-0		

General standards

Connector standard	IEC 61076-3-117 Var. 14
--------------------	-------------------------

Technical specifications for hybrid connector

Contact material (hybrid connector)	Copper alloy	Contact resistance (hybrid connector)	≤ 10 mΩ
Housing base material (hybrid connector)	Zinc diecast (flange), PA 66	Material of seal (hybrid connector)	NBR
Plugging cycles (hybrid connector)	500	Pole count	10
Protection degree (hybrid connector)	IP65	Rated current (hybrid connector)	3 A per contact
Rated voltage (DIN EN 61984) (hybrid connector)	24 V	Shielding (hybrid connector)	360° shield contact

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-03-92	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format