

THM MT30X 17.5/17.5 SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

| | |
|--------------------|---|
| Version | THM, Device markers, 17.5 x 17.5 mm, silver |
| Order No. | 1338280000 |
| Type | THM MT30X 17.5/17.5 SI |
| GTIN (EAN) | 4050118142839 |
| Qty. | 1 Stück |
| compatible printer | 2599430000 2599440000 |

Erstellungs-Datum May 16, 2023 11:24:54 AM CEST

THM MT30X 17.5/17.5 SI

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 17.5 mm | Height (inches) | 0.689 inch |
| Width | 17.5 mm | Width (inches) | 0.689 inch |
| Net weight | 611 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|-----------------------------|-----------------------------------|-------------------------------|
| Adhesive | Acrylate adhesive | Approval acc. to UL 969 | Yes |
| Colour | silver | Halogen | No |
| Material | Polyester | Number of markers per combination | 1 Label reel = Device markers |
| Number per roll | 5,000 | Operating temperature range | -40...150 °C |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Printing method | Thermal transfer | UL 94 flammability rating | V-0 |
| Version | Self-adhesive, halogen-free | Width | 17.5 mm |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |

THM MT30X 17.5/17.5 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

