

WM4 C I SET**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

Version	Photovoltaics, Plug-in connector, For crimping tool
Order No.	1344960000
Type	WM4 C I SET
GTIN (EAN)	4050118149036
Qty.	1 pc(s).

WM4 C I SET

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 23 g

Temperatures

Continuous operating temp., min. -40 °C Continuous operating temp., max. 85 °C

Technical data

Approvals	TÜV Rheinland (IEC 62852)	Conductor cross-section, max.	6 mm ²
Conductor cross-section, min.	4 mm ²	External thread	M 12
Outer cable diameter, max.	7 mm	Outer cable diameter, min.	5.5 mm
Pollution severity	2	Protection degree	IP65, IP67, IP2x open
Rated current	35 A	Rated voltage	1500 V DC (IEC)

Classifications

ETIM 6.0	EC002928	ETIM 7.0	EC002928
ETIM 8.0	EC002928	ECLASS 9.0	22-57-92-03
ECLASS 9.1	27-44-01-07	ECLASS 10.0	27-44-01-07
ECLASS 11.0	22-57-02-92	ECLASS 12.0	22-57-02-92

Approvals

ROHS Conform

Downloads

Approval/Certificate/Document of Conformity	WM4 C TÜV certificate
Engineering Data	CAD data – STEP
User Documentation	PV Stecker
Catalogues	Catalogues in PDF-format