

## PAC-UNIV-HE40-HE40-4M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

Version	Pre-assembled cable, PAC
Order No.	<a href="#">1349700040</a>
Type	PAC-UNIV-HE40-HE40-4M
GTIN (EAN)	4032248249107
Qty.	1 pc(s).

Creation date March 17, 2023 10:44:00 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

## PAC-UNIV-HE40-HE40-4M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight 568.3 g

### Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C
Operating temperature, min.	-10 °C	Operating temperature, max.	50 °C

### General Data

Cable	Cable LiYY	Cable length	4 m
Connector PLC side	FLAT CABLE PLANO HE10 40P	Interface connector	FLAT CABLE PLANO HE10 40P
Material	PVC	Number of poles, min.	40-pole
Outer diameter	11.7 ± 1 mm	Suitable for	Digital signals
Wire cross-section	0.14 mm <sup>2</sup>		

### Electrical Data

Capacity wire / shield	300 pF/m	Capacity wire / wires	300 pF/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150mΩ/m
Total current, max.	3 A		

### Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

### Approvals

ROHS Conform

### Downloads

Catalogues [Catalogues in PDF-format](#)