

PAC-UNIV-HE20-F-2M5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|----------------------------|
| Version | Pre-assembled cable, PAC |
| Order No. | 1349790025 |
| Type | PAC-UNIV-HE20-F-2M5 |
| GTIN (EAN) | 4032248301119 |
| Qty. | 1 pc(s). |

Creation date March 17, 2023 10:53:35 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

PAC-UNIV-HE20-F-2M5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 177 g

Temperatures

| | | | |
|-----------------------------|-------------|-----------------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
| Operating temperature, min. | -10 °C | Operating temperature, max. | 50 °C |

General Data

| | | | |
|--------------------|---|-----------------------|---------------------------------|
| Cable | Cable LiYY | Cable length | 2.5 m |
| Connector PLC side | H0.14/10 (FERRULES 0.14mm ²) | Interface connector | FLAT CABLE CONECTOR HE10 20P |
| Material | PVC | Number of poles, min. | 20-pole |
| Outer diameter | 8.6 ± 1 mm | Suitable for | Digital signals |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|------------------------|---------------------|--|-----------|
| Capacity wire / shield | 300 pF/m | Capacity wire / wires | 300 pF/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 V DC ≤ 25 V AC | Resistance | ≤ 150mΩ/m |
| Total current, max. | 3 A | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000237 | ETIM 7.0 | EC000237 |
| ETIM 8.0 | EC000237 | ECLASS 9.0 | 27-24-22-20 |
| ECLASS 9.1 | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|--------------------|--|
| User Documentation | Colours chart |
| Catalogues | Catalogues in PDF-format |