

BG GHDE LED TL PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Energy-efficient basic lighting with a long service life

- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to one side
- 5W Power

Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm²

General ordering data

Order No.	1390850000
Type	BG GHDE LED TL PT6
GTIN (EAN)	4050118190977

BG GHDE LED TL PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	46 mm	Height (inches)	1.811 inch
Width	104 mm	Width (inches)	4.094 inch
Length	181 mm	Length (inches)	7.126 inch
Net weight	616 g		

Temperatures

Operating temperature	-40 °C...60 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	60 °C		

General data

Amplitude of acceleration	5 m/s ² (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Circuit breaker	< 10 A	Halogen	yes (PVC cable)
Height	≤ 3000 m	Insulation voltage	< 500 V (housing/PE)
Line type	Heluwind WK 103w-T 3G1,5 (AD 8 mm)	Mounting position, installation notice	Arbitrary
Peak acceleration, type L	70 m/s ²	Pollution severity	2
Protection class	II	Protection degree	IP65 with corresponding housing
Shock resistance EN 60721-3-3	Class 3M3	Short-circuit protection	internal
Silicone	No	Surge voltage category	II
Type of connection	Open cable end/length 2 m	UL 94 flammability rating	V-0
Vibration resistance EN 60721-3-3	Class 3M3, EN 60721-3-3		

Rated data acc. to IEC 60598-1

Input voltage	100...265 V DC (45...65 Hz)	Inrush current	0.5 A @ 0.1 ms
Power loss	< 2 W	Power rating	7 W
Rated voltage	265		

Classifications

ETIM 6.0	EC001959	ETIM 7.0	EC001959
ETIM 8.0	EC001959	ECLASS 9.0	27-11-06-40
ECLASS 9.1	27-11-06-40	ECLASS 10.0	27-11-06-40
ECLASS 11.0	27-11-06-40	ECLASS 12.0	27-11-06-40

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	730dada5-5c8b-4737-8e0b-847db05af8d5

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E345151

Erstellungs-Datum May 25, 2023 11:40:29 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

BG GHDE LED TL PT6

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Approval/Certificate/Document of
Conformity

[FieldPower LED](#)

Catalogues

[Catalogues in PDF-format](#)

BG GHDE LED TL PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Zeichnungen

