

## BG GHDE LED TL PTS 4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Energy-efficient basic lighting with a long service life

- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to one side
- 5W Power

### Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm<sup>2</sup>

### General ordering data

Order No.	<a href="#">1390880000</a>
Type	BG GHDE LED TL PTS 4
GTIN (EAN)	4050118190984

## BG GHDE LED TL PTS 4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Height	46 mm	Height (inches)	1.811 inch
Width	104 mm	Width (inches)	4.094 inch
Length	181 mm	Length (inches)	7.126 inch
Net weight	418 g		

### Temperatures

Operating temperature	-40 °C...60 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	60 °C		

### General data

Amplitude of acceleration	5 m/s <sup>2</sup> (@ 9-200 Hz)	Amplitude of deflection	1.5 mm (2-9 Hz)
Halogen	yes (PVC cable)	Height	≤ 3000 m
Insulation voltage	< 500 V (housing/PE)	Mounting position, installation notice	Arbitrary
Peak acceleration, type L	70 m/s <sup>2</sup>	Pollution severity	2
Protection class	II	Protection degree	IP65 with corresponding housing
Shock resistance EN 60721-3-3	EN 60721-3-3, Class 3M3 portable	Short-circuit protection	internal
Silicone	No	Surge voltage category	II
Type of connection	FieldPower® plug PTS 4	UL 94 flammability rating	V-0
Vibration resistance EN 60721-3-3	Class 3M3, EN 60721-3-3		

### Rated data acc. to IEC 60598-1

Input voltage	100...265 V DC (45...65 Hz)	Inrush current	0.5 A @ 0.1 ms
Power loss	< 2 W	Power rating	7 W
Rated voltage	265		

### Classifications

ETIM 6.0	EC001959	ETIM 7.0	EC001959
ETIM 8.0	EC001959	ECLASS 9.0	27-11-06-40
ECLASS 9.1	27-11-06-40	ECLASS 10.0	27-11-06-40
ECLASS 11.0	27-11-06-40	ECLASS 12.0	27-11-06-40

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	730dada5-5c8b-4737-8e0b-847db05af8d5

### Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E345151

## BG GHDE LED TL PTS 4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Approval/Certificate/Document of  
Conformity

[FieldPower LED](#)

Catalogues

[Catalogues in PDF-format](#)

## BG GHDE LED TL PTS 4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

