

KLBUE 3-8 RC TS27

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Product image



Shielding and earthing

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, PA 66 GF 30
Order No.	1403070000
Type	KLBUE 3-8 RC TS27
GTIN (EAN)	4050118204780
Qty.	1 Stück

Erstellungs-Datum May 25, 2023 12:32:17 PM CEST

KLBUE 3-8 RC TS27

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	50 mm	Depth (inches)	1.969 inch
Height	67.5 mm	Height (inches)	2.657 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	61.19 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-25
Continuous operating temp., max.	105		

Material data

Material	PA 66 GF 30	Colour	black, Silver grey
UL 94 flammability rating	V-0		

System specifications

Version	For a shield connection, With resistor	Rail	TS 27
---------	---	------	-------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

Conductors for clamping (rated connection)

Cable diameter, max.	8 mm	Cable diameter, min.	3 mm
Stripping length	22 mm		

General

Installation advice	Direct mounting	Rail	TS 27
---------------------	-----------------	------	-------

Rating data

Rated voltage	230 V AC
---------------	----------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6fc8563f-82a2-46cf-b3da-0e2c7ddd4382

KLBUE 3-8 RC TS27

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, EPLAN](#)

User Documentation

[Beipackzettel_KLBUE_RC.pdf](#)
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

KLBUE 3-8 RC TS27

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

