

THM WO VIN 25.4/95.2 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

| | |
|------------|---|
| Version | THM, Conductor and cable markers, 12.7 mm, 25.4 x 95.3 mm, white / yellow |
| Order No. | 1420020000 |
| Type | THM WO VIN 25.4/95.2 BL |
| GTIN (EAN) | 4050118223514 |
| Qty. | 1 Stück |

Erstellungs-Datum May 16, 2023 11:35:27 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

THM WO VIN 25.4/95.2 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 0.065 mm | Depth (inches) | 0.003 inch |
| Height | 25.4 mm | Height (inches) | 1 inch |
| Width | 95.3 mm | Width (inches) | 3.752 inch |
| Net weight | 545 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -40...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|-----------------------|-----------------------------------|--|
| Adhesive | Polyacrylate adhesive | Approval acc. to UL 969 | No |
| Colour | white / yellow | Halogen | Yes |
| Material | Vinyl film | Number of markers per combination | 1 Label reel = Conductor and cable markers |
| Number per roll | 1,000 | Operating temperature range | -40...80 °C |
| Operating temperature range, max. | 80 °C | Operating temperature range, min. | -40 °C |
| Printing | Lightning | Size of labelling field | 40 x 25.4 mm |
| UL 94 flammability rating | V-0 | Version | Self-adhesive |
| Width | 95.3 mm | | |

Conductor and cable markers

| | | | |
|----------------------------------|----------------------------|-------------------------------|----------------------|
| Conductor O.D. | 12.7 mm | Conductor O.D., max. | 12.7 mm |
| Conductor cross-section, max. | 120 mm ² | Conductor cross-section, min. | 0.75 mm ² |
| Cross-section for connected wire | 0.75 - 120 mm ² | Halogen | Yes |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ECLASS 9.0 | 27-40-04-01 |
| ECLASS 9.1 | 27-40-04-01 | ECLASS 10.0 | 27-40-04-01 |
| ECLASS 11.0 | 27-28-11-02 | ECLASS 12.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

THM WO VIN 25.4/95.2 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

