

ZQV 1.5N/R12.8/10 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	TERMSERIES, Cross-connector
Order No.	1445940000
Type	ZQV 1.5N/R12.8/10 SW
GTIN (EAN)	4032248180301
Qty.	10 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2021-06-30
Alternative product	2556500000

Creation date March 8, 2023 11:09:12 AM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

ZQV 1.5N/R12.8/10 SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	4.9 mm	Depth (inches)	0.193 inch
Height	13.1 mm	Height (inches)	0.516 inch
Width	119 mm	Width (inches)	4.685 inch
Net weight	6 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...60 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	60 °C

Rated data UL

Rated current (UL)	10 A
--------------------	------

General data

Version	can be cut to length	Colour	black
---------	----------------------	--------	-------

Insulation coordination

Rated voltage	250 V
---------------	-------

Connection data

Pitch in mm (P)	12.8 mm
-----------------	---------

Classifications

ETIM 6.0	EC002586	ETIM 7.0	EC002586
ETIM 8.0	EC002586	ECLASS 9.1	27-37-16-92
ECLASS 10.0	27-37-16-92	ECLASS 11.0	27-37-16-92
ECLASS 12.0	27-37-16-92		

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	Beipackzettel / Package Insert - multilingual
Catalogues	Catalogues in PDF-format

Data sheet

ZQV 1.5N/R12.8/10 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing

