

**IE-FSMD2UE0010MSDESDEX****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO breakout cable

**General ordering data**

Version	Dragline cable, SC IP 67 PushPull V14 metal, SC IP 67 PushPull V14 metal, 9 µm, PUR, 10 m
Order No.	<a href="#">1449420100</a>
Type	IE-FSMD2UE0010MSDESDEX
GTIN (EAN)	4050118502008
Qty.	1 Stück

**IE-FSMD2UE0010MSDESDEX**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	10 m	Length (inches)	393.701 inch
Net weight	0.01 g		

**Temperatures**

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C
Installation temperature	-20 °C...60 °C		

**Cable structure**

Cable layout	Break-out dragline	Core diameter	9 µm
Material sheath	PUR	Primary coating	245 µm
Sheath diameter	6 mm	Sheathing colour	black

**Mechanical and material properties of cable**

Bending cycles	100,000	Halogen	No
Min. bending radius, once only	25 mm	Min. bending radius, repetitive	77 mm

**Plug**

Plug	Cable side	left
	Version of contact face	SC
	Protection degree (IP)	IP67
	Gender of contact	male contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	No
	Cable side	right
	Version of contact face	SC
	Protection degree (IP)	IP67
	Gender of contact	male contact
	Outlet direction	straight
	Housing version	PushPull V14
	Version of connector	plug
	Housing main material	Zinc diecast
	Status indicator available	No
	Shielding available	No

Plug left SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded

Plug right SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded

**Plug, left**

Connector left	Plug left	SC, IP67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded
	SC IP 67 PushPull V14 metal	

**IE-FSMD2UE0010MSDESDEX**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

**Technische Daten**

**Plug, right**

Connector right	Plug right	www.weidmueller.com	SC IP 67, male contact, straight, PushPull V14, plug, Zinc diecast, unshielded
	SC IP 67 PushPull V14 metal		

**Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**IE-FSMD2UE0010MSDESDEX**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Detailed drawing**

