

IE-C6KS8VG0100XCSXXX-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables, PROFINET, Cat 6_A, PVC, green,
M12 X-type

General ordering data

Version	Connecting line, M12 X-type IP 67 straight male, Open, Cat.6 _A / Class E _A (ISO/IEC 11801 2010), PVC, 10 m
Order No.	1449470100
Type	IE-C6KS8VG0100XCSXXX-E
GTIN (EAN)	4050118264180
Qty.	1 pc(s).

Creation date March 13, 2023 2:09:29 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-C6KS8VG0100XCSXXX-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	10 m	Length (inches)	393.701 inch
Net weight	0.1 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...80 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	80 °C
Installation temperature	-40 °C...80 °C		

Cable specific standards

Standard, assembly	UL-Style 2461
--------------------	---------------

Standards

Standard, assembly	UL-Style 2461
--------------------	---------------

Cable structure

Colour sequence or wires - wire pairs	white/blue - blue, white/ orange - orange, white/ green - green, white/ brown - brown	Cross-section	4*2*AWG 23/7
Insulation cross-section	1.58 mm	Material sheath	PVC
Sheath diameter, max.	8.8 mm	Sheathing colour	green (RAL 6018)
Shielding	S/FTP		

Electrical properties of cable

Category	Cat.6 _A / Class E _A (ISO/IEC 11801 2010)	Speed	10 GBit/s
Test voltage: wire-wire-shield	800 V _{eff} , 50 Hz, 1 min		

Mechanical and material properties of cable

Halogen	Yes	Min. bending radius, once only	4 x cable diameter
Min. bending radius, repetitive	8 x cable diameter	Pulling force	≤ 150 N
Resistance to spread of flame	in accordance with IEC 60332-1-2	Speed	10 GBit/s

Plug

Plug left	M12, X, IP67, male contact, straight, plug, Plastic, shielded	Plug right	free conductor end
-----------	---------------------------------------------------------------------	------------	--------------------

Plug, left

Connector left	M12 X-type IP 67 straight male
----------------	-----------------------------------

Plug, right

Connector right	Open
-----------------	------

Creation date March 13, 2023 2:09:29 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

2

IE-C6KS8VG0100XCSXXX-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Classifications**

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	PROFINET Manufacturer's Declaration
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

Data sheet

IE-C6KS8VG0100XCSXXX-E

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

White, Orange	1	M12
Orange	2	
White, Green	3	
Green	4	
White, Brown	5	
Brown	6	
White, Blue	7	
Blue	8	
