

## WFSKHV/0,5-1,05

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

### General ordering data

Version	cable lug, terminal end, Insulated cable connector, 0.5 mm <sup>2</sup> - 1 mm <sup>2</sup>
Order No.	<a href="#">1491960000</a>
Type	WFSKHV/0,5-1,05
GTIN (EAN)	4050118301977
Qty.	100 Stück

Erstellungs-Datum May 16, 2023 12:26:35 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## WFSKHV/0,5-1,05

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 1.26 g

### Connectors

Conductor cross-section, max.	1 mm <sup>2</sup>	Conductor cross-section, min.	0.5 mm <sup>2</sup>
Identification colour	red	Insulation	Fully insulated
Length 1 (l1)	16.3 mm	Material/plastic	PA
Plug-in density (d3)	0.8 mm	Plug-in width (d2)	6.3 mm

### Classifications

ETIM 6.0	EC0005 16	ETIM 7.0	EC0005 16
ETIM 8.0	EC0005 16	ECLASS 9.0	27-44-03-92
ECLASS 9.1	27-40-02-90	ECLASS 10.0	27-44-03-92
ECLASS 11.0	27-44-03-92	ECLASS 12.0	27-44-03-92

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Approvals

ROHS Conform

### Downloads

Engineering Data [EPLAN](#)  
 Catalogues [Catalogues in PDF-format](#)  
 Brochures

**WFSKHV/0,5-1,05**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

