

WFSKHV/1,5-2,5

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Insulated cable connector in PVC or PC/PA

- Conventional designs
- Not soldered
- With conical entry funnel, except for joint connector

General ordering data

Version	cable lug, terminal end, Insulated cable connector, 1.5 mm ² - 2.5 mm ²
Order No.	1491970000
Type	WFSKHV/1,5-2,5
GTIN (EAN)	4050118301755
Qty.	100 Stück

Erstellungs-Datum May 16, 2023 12:26:44 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

WFSKHV/1,5-2,5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1.27 g

Connectors

Conductor cross-section, max.	2.5 mm ²	Conductor cross-section, min.	1.5 mm ²
Identification colour	blue	Insulation	Fully insulated
Length 1 (l1)	16.3 mm	Material/plastic	PA
Plug-in density (d3)	0.8 mm	Plug-in width (d2)	6.3 mm

Classifications

ETIM 6.0	EC0005 16	ETIM 7.0	EC0005 16
ETIM 8.0	EC0005 16	ECLASS 9.0	27-44-03-92
ECLASS 9.1	27-40-02-90	ECLASS 10.0	27-44-03-92
ECLASS 11.0	27-44-03-92	ECLASS 12.0	27-44-03-92

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

ROHS Conform

Downloads

Engineering Data [EPLAN](#)
 Catalogues [Catalogues in PDF-format](#)
 Brochures

WFSKHV/1,5-2,5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

