

KWN-M14/-35 90**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end,35 mm ²
Order No.	1494640000
Type	KWN-M14/-35 90
GTIN (EAN)	4050118304350
Qty.	100 Stück

Erstellungs-Datum May 16, 2023 12:31:35 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

KWN-M14/-35 90

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 24.79 g

Technical data

Version Euro series 90°

Connectors

Conductor cross-section	35 mm ²	Connection length (l)	23.5 mm
Flange width (b)	23 mm	Hole	M 14
Inside diameter of flange (d2)	15 mm	Inside diameter of shaft (d1)	8.5 mm
Insulation	not available	Outside diameter of shaft (d3)	12 mm
Shaft length (a)	16 mm		

Classifications

ETIM 6.0	EC001051	ETIM 7.0	EC001051
ETIM 8.0	EC001051	ECLASS 9.0	27-40-02-05
ECLASS 9.1	27-40-02-05	ECLASS 10.0	27-40-02-05
ECLASS 11.0	27-40-02-05	ECLASS 12.0	27-40-02-05

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

KWN-M14/-35 90

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

