

KRN-M8/-50 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end,50 mm ²
Order No.	1494830000
Type	KRN-M8/-50 S
GTIN (EAN)	4050118304404
Qty.	25 Stück

KRN-M8/-50 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 26.64 g

Technical data

Version Euro series, narrow flange

Connectors

Conductor cross-section	50 mm ²	Connection length (l)	39 mm
Flange width (b)	17 mm	Hole	M8
Inside diameter of flange (d2)	8.4 mm	Inside diameter of shaft (d1)	10 mm
Insulation	not available	Outside diameter of shaft (d3)	14 mm
Shaft length (a)	19 mm		

Classifications

ETIM 6.0	EC001051	ETIM 7.0	EC001051
ETIM 8.0	EC001051	ECLASS 9.0	27-40-02-05
ECLASS 9.1	27-40-02-05	ECLASS 10.0	27-40-02-05
ECLASS 11.0	27-40-02-05	ECLASS 12.0	27-40-02-05

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

KRN-M8/-50 S

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

