

KRN-M3/-0,75**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end, 0.5 mm ² - 0.75 mm ²
Order No.	1495010000
Type	KRN-M3/-0,75
GTIN (EAN)	4050118304800
Qty.	100 Stück

Erstellungs-Datum May 16, 2023 12:36:21 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

KRN-M3/-0,75

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 0.73 g

Technical data

Version Euro series, standard

Connectors

Conductor cross-section, max.	0.75 mm ²	Conductor cross-section, min.	0.5 mm ²
Connection length (l)	12.5 mm	Flange width (b)	6.5 mm
Hole	M 3	Inside diameter of flange (d2)	3.2 mm
Inside diameter of shaft (d1)	1.4 mm	Insulation	not available
Outside diameter of shaft (d3)	3 mm	Shaft length (a)	6 mm

Classifications

ETIM 6.0	EC001051	ETIM 7.0	EC001051
ETIM 8.0	EC001051	ECLASS 9.0	27-40-02-05
ECLASS 9.1	27-40-02-05	ECLASS 10.0	27-40-02-05
ECLASS 11.0	27-40-02-05	ECLASS 12.0	27-40-02-05

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

Datenblatt

KRN-M3/-0,75

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

