

## KWN-M10/-70 90

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

### General ordering data

Version	cable lug, terminal end,70 mm <sup>2</sup>
Order No.	<a href="#">1496030000</a>
Type	KWN-M10/-70 90
GTIN (EAN)	4050118305432
Qty.	25 Stück

Erstellungs-Datum May 16, 2023 12:50:07 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## KWN-M10/-70 90

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 49.88 g

### Technical data

Version Euro series 90°

### Connectors

Conductor cross-section	70 mm <sup>2</sup>	Connection length (l)	22.8 mm
Flange width (b)	24 mm	Hole	M10
Inside diameter of flange (d2)	10.5 mm	Inside diameter of shaft (d1)	12 mm
Insulation	not available	Outside diameter of shaft (d3)	16.5 mm
Shaft length (a)	20 mm		

### Classifications

ETIM 6.0	EC001051	ETIM 7.0	EC001051
ETIM 8.0	EC001051	ECLASS 9.0	27-40-02-05
ECLASS 9.1	27-40-02-05	ECLASS 10.0	27-40-02-05
ECLASS 11.0	27-40-02-05	ECLASS 12.0	27-40-02-05

### Approvals

Approvals



ROHS Conform

### Downloads

Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## KWN-M10/-70 90

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

