

KP-M10/-10

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end, 10 mm ²
Order No.	1497910000
Type	KP-M10/-10
GTIN (EAN)	4050118307276
Qty.	100 Stück

KP-M10/-10

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 3.981 g

Technical data

Version DIN series 46235, standard

Connectors

Conductor cross-section	10 mm ²	Connection length (l)	29 mm
Flange width (b)	15 mm	Hole	M10
Identification number Cu	6 K	Inside diameter of flange (d2)	10.5 mm
Inside diameter of shaft (d1)	4.4 mm	Insulation	not available
Outside diameter of shaft (d3)	6 mm	Shaft length (a)	10 mm

Classifications

ETIM 6.0	EC001050	ETIM 7.0	EC001050
ETIM 8.0	EC001050	ECLASS 9.0	27-40-02-03
ECLASS 9.1	27-40-02-03	ECLASS 10.0	27-40-02-03
ECLASS 11.0	27-40-02-03	ECLASS 12.0	27-40-02-03

Approvals

ROHS Conform

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

KP-M10/-10

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

