

KP-M20/-70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Version	cable lug, terminal end,70 mm ²
Order No.	1498170000
Type	KP-M20/-70
GTIN (EAN)	4050118307344
Qty.	50 Stück

KP-M20/-70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 69.46 g

Technical data

Version DIN series 46235,
 standard

Connectors

Conductor cross-section	70 mm ²	Connection length (l)	61 mm
Flange width (b)	31 mm	Hole	M 20
Identification number Cu	16 K	Inside diameter of flange (d2)	21 mm
Inside diameter of shaft (d1)	11.3 mm	Insulation	not available
Outside diameter of shaft (d3)	16.5 mm	Shaft length (a)	28 mm

Classifications

ETIM 6.0	EC001050	ETIM 7.0	EC001050
ETIM 8.0	EC001050	ECLASS 9.0	27-40-02-03
ECLASS 9.1	27-40-02-03	ECLASS 10.0	27-40-02-03
ECLASS 11.0	27-40-02-03	ECLASS 12.0	27-40-02-03

Approvals

ROHS Conform

Downloads

Engineering Data [EPLAN](#)
 Catalogues [Catalogues in PDF-format](#)
 Brochures

KP-M20/-70

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

