

**KP-M20/-185****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Version	cable lug, terminal end, 185 mm <sup>2</sup>
Order No.	<a href="#">1498380000</a>
Type	KP-M20/-185
GTIN (EAN)	4050118307757
Qty.	25 Stück

## KP-M20/-185

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 189.8 g

### Technical data

Version DIN series 46235,  
 standard

### Connectors

Conductor cross-section	185 mm <sup>2</sup>	Connection length (l)	83 mm
Flange width (b)	40 mm	Hole	M 20
Identification number Cu	25 K	Inside diameter of flange (d2)	21 mm
Inside diameter of shaft (d1)	19 mm	Insulation	not available
Outside diameter of shaft (d3)	25.5 mm	Shaft length (a)	40 mm

### Classifications

ETIM 6.0	EC001050	ETIM 7.0	EC001050
ETIM 8.0	EC001050	ECLASS 9.0	27-40-02-03
ECLASS 9.1	27-40-02-03	ECLASS 10.0	27-40-02-03
ECLASS 11.0	27-40-02-03	ECLASS 12.0	27-40-02-03

### Approvals

ROHS Conform

### Downloads

Engineering Data [EPLAN](#)  
 Catalogues [Catalogues in PDF-format](#)  
 Brochures

**KP-M20/-185**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

