

KP-M14/-150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

| | |
|------------|--|
| Version | cable lug, terminal end, 150 mm ² |
| Order No. | 1498580000 |
| Type | KP-M14/-150 |
| GTIN (EAN) | 4050118308112 |
| Qty. | 25 Stück |

KP-M14/-150

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 164.92 g

Technical data

Version DIN series 46235,
 standard

Connectors

| | | | |
|--------------------------------|---------------------|--------------------------------|---------------|
| Conductor cross-section | 150 mm ² | Connection length (l) | 78 mm |
| Flange width (b) | 34 mm | Hole | M 14 |
| Identification number Cu | 22 K | Inside diameter of flange (d2) | 15 mm |
| Inside diameter of shaft (d1) | 17 mm | Insulation | not available |
| Outside diameter of shaft (d3) | 23.5 mm | Shaft length (a) | 35 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001050 | ETIM 7.0 | EC001050 |
| ETIM 8.0 | EC001050 | ECLASS 9.0 | 27-40-02-03 |
| ECLASS 9.1 | 27-40-02-03 | ECLASS 10.0 | 27-40-02-03 |
| ECLASS 11.0 | 27-40-02-03 | ECLASS 12.0 | 27-40-02-03 |

Approvals

ROHS Conform

Downloads

Engineering Data [EPLAN](#)
 Catalogues [Catalogues in PDF-format](#)
 Brochures

KP-M14/-150

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

