

**ES APG 80 DIN 10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

**General ordering data**

Version	10mm <sup>2</sup> , Indent crimp
Order No.	<a href="#">1502830000</a>
Type	ES APG 80 DIN 10
GTIN (EAN)	4050118310948
Qty.	1 Stück

## ES APG 80 DIN 10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 349.3 g

### Crimp inserts

Crimp cross-section copper	10	Crimping width	8 mm
Crimping width in mm	8		

### Description of contact

Conductor cross-section, max. AWG	8	Crimping range, max.	10 mm <sup>2</sup>
-----------------------------------	---	----------------------	--------------------

### tool data crimping

Cable lug cross section	nominal	10 mm <sup>2</sup>
Crimping type/profile	Indent crimp	

### Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90

### Environmental Product Compliance

REACH SVHC Lead 7439-92-1

### Downloads

Catalogues [Catalogues in PDF-format](#)  
 Brochures