

ES APG 80 DIN 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm²
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

General ordering data

Version	35mm ² , Indent crimp
Order No.	1502870000
Type	ES APG 80 DIN 35
GTIN (EAN)	4050118310474
Qty.	1 Stück

ES APG 80 DIN 35

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 351.7 g

Crimp inserts

Crimp cross-section copper	35	Crimping width	11 mm
Crimping width in mm	11		

Description of contact

Conductor cross-section, max. AWG	2	Crimping range, max.	35 mm ²
-----------------------------------	---	----------------------	--------------------

tool data crimping

Cable lug cross section	nominal	35 mm ²
Crimping type/profile	Indent crimp	

Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ECLASS 9.0	21-04-90-90
ECLASS 9.1	21-01-90-90	ECLASS 10.0	21-04-90-90
ECLASS 11.0	21-04-90-90	ECLASS 12.0	21-04-90-90

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Downloads

Catalogues [Catalogues in PDF-format](#)
 Brochures