

LADEGERAET EPG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

General ordering data

Version	
Order No.	1509370000
Type	LADEGERAET EPG
GTIN (EAN)	4050118318630
Qty.	1 Stück

LADEGERAET EPG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	178 mm	Depth (inches)	7.008 inch
Height	78 mm	Height (inches)	3.071 inch
Width	150 mm	Width (inches)	5.905 inch
Net weight	512 g		

Technical data

Charging time	0.5 h	Electrical connection	100 - 240 V AC / 50/60 Hz
Power consumption	90 W	Voltage range	12 / 14.4 / 18 V

Classifications

ETIM 6.0	EC000359	ETIM 7.0	EC000359
ETIM 8.0	EC000359	ECLASS 9.1	21-05-92-01
ECLASS 10.0	21-05-92-01	ECLASS 11.0	21-05-29-01
ECLASS 12.0	21-05-29-01		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	