

**ZQV 4N/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Order No.  | <a href="#">1528090000</a> |
| Type       | ZQV 4N/10                  |
| GTIN (EAN) | 4050118332896              |
| Qty.       | 20 pc(s).                  |

**ZQV 4N/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 27.95 mm | Depth (inches)  | 1.1 inch   |
| Height     | 2.8 mm   | Height (inches) | 0.11 inch  |
| Width      | 58.7 mm  | Width (inches)  | 2.311 inch |
| Net weight | 7.348 g  |                 |            |

**Temperatures**

|                                  |                |                                  |                 |
|----------------------------------|----------------|----------------------------------|-----------------|
| Storage temperature              | -25 °C...55 °C | Operating temperature            | -60 °C...130 °C |
| Operating temperature, min.      | -60 °C         | Operating temperature, max.      | 130 °C          |
| Continuous operating temp., min. | -60            | Continuous operating temp., max. | 130             |

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

**Additional technical data**

|                          |     |                |         |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

**Cross-connector**

|                                     |      |                       |                 |
|-------------------------------------|------|-----------------------|-----------------|
| Number of cross-connected terminals | 10   | Rated current, 2-pole | 32 A            |
| Rated current, multi-pole           | 32 A | Type                  | Cross-connector |

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 6.1 mm |
|-----------------|--------|

**General**

|                 |    |
|-----------------|----|
| Number of poles | 10 |
|-----------------|----|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

**Important note**

|                     |   |
|---------------------|---|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|---|

## ZQV 4N/10

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

# Technical data

## Approvals

Approvals



ROHS

Conform

## Downloads

Approval/Certificate/Document of Conformity

- [EAC certificate](#)
- [DNVGL certificate](#)
- [BV certificate](#)
- [RINA certificate](#)
- [Lloyds Register Certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[2434520000\\_BED-ANL\\_ZQV\\_A\\_REIHE.pdf](#)  
[StorageConditionsTerminalBlocks](#)  
[BPZL ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures