

IE-FC-SET-IPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

| | |
|-------------------|--|
| Version | FrontCom, Set |
| Order No. | 1543680000 |
| Type | IE-FC-SET-IPDEK001-KY-P |
| GTIN (EAN) | 4050118348842 |
| Qty. | 1 pc(s). |
| Reference product | 1450520000 1450630000 1450730000 1019570000 1962840000 1450820000 |

Creation date March 8, 2023 1:27:40 PM CET

Catalogue status 03.03.2023 / We reserve the right to make technical changes.

IE-FC-SET-IPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 134 mm | Depth (inches) | 5.276 inch |
| Height | 40 mm | Height (inches) | 1.575 inch |
| Width | 67 mm | Width (inches) | 2.638 inch |
| Net weight | 493.15 g | | |

General data

| | | | |
|-------------------|-----------------------|----------------------------------|--|
| Material cover | Polycarbonate PC | | |
| Material frame | Zinc diecast | | |
| Product type | Set | | |
| Protection degree | IP65, in closed state | | |
| Reference product | Cardinality | 1 | |
| | Reference | IE-FC-SFP-KEY2 | |
| | Cardinality | 1 | |
| | Reference | IE-FC-IP-PWB/2ST | |
| | Cardinality | 1 | |
| | Reference | IE-FC-I-PWB-DE | |
| | Cardinality | 1 | |
| | Reference | IE-BI-USB-A | |
| | Cardinality | 1 | |
| Reference product | Reference | IE-BI-RJ45-C | |
| | Cardinality | 1 | |
| | Reference | IE-FC-PWPC | |

Technical data

| | | | |
|--------------------------|---|--------------------------|----------------------------------|
| Data inserts | USB 2.0 A/A, RJ45 coupling Cat.6 _A | Frame | Plastic cover, Lockable with key |
| Insert plate | 2x data, 1x power, Unshielded | Power inserts | Socket DE |
| Printing | Incl. fixed inscription: "Service only!", "USB", "Ethernet", "230 V AC" | Rated current for socket | 16 A |
| Rated voltage for socket | 250 V | | |

General standards

Certificate No. (DNVGL) TAA000022B

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001031 | ETIM 7.0 | EC001031 |
| ETIM 8.0 | EC001031 | ECLASS 9.0 | 27-18-27-02 |
| ECLASS 9.1 | 27-18-27-90 | ECLASS 10.0 | 27-18-27-02 |
| ECLASS 11.0 | 27-18-27-02 | ECLASS 12.0 | 27-18-28-92 |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
 SCIP 3767b26f-703a-492e-9234-36e83d1c0725

IE-FC-SET-IPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS Conform

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | GL FrontCom |
| Engineering Data | CAD data – STEP |
| User Documentation | MAN IE GUIDE DE MAN IE GUIDE EN |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN |

Data sheet

IE-FC-SET-IPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

