

**CAN SUB-D M12 TERM PS**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Similar to illustration**



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

**General ordering data**

Version	SUB-D
Order No.	<a href="#">1555280000</a>
Type	CAN SUB-D M12 TERM PS
GTIN (EAN)	4050118361094
Qty.	1 Stück

**CAN SUB-D M12 TERM PS**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Technische Daten**

**Dimensions and weights**

Depth	16.8 mm	Depth (inches)	0.661 inch
Height	59 mm	Height (inches)	2.323 inch
Width	46.5 mm	Width (inches)	1.831 inch
Net weight	89 g		

**Temperatures**

Humidity	Max. 75% at +25°C, non-condensing
----------	-----------------------------------

**Technical specifications for sub-D connector**

BUS PG interface	D-Sub 9-pole, Pin	BUS interface	D-Sub 9-pole, Socket
BUS, cable interface	M12 A-coded, pin + socket	Data rate	1 Mbps
Housing main material	ZnAl	Humidity	Max. 75% at +25°C, non-condensing
Interlock	UNC4-40	Outgoing elbow	90°
Plugging cycles	≥ 200	Programming interface	Yes
Protection degree	IP30	Temperature range of housing	-20...+70 ° C
Terminating resistor available	Yes		

**Classifications**

ETIM 6.0	EC001132	ETIM 7.0	EC001132
ETIM 8.0	EC001132	ECLASS 9.0	27-44-03-02
ECLASS 9.1	27-44-03-90	ECLASS 10.0	27-44-03-02
ECLASS 11.0	27-44-03-02	ECLASS 12.0	27-44-03-02

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	3cc1d9b1-0f2a-47ed-a501-ddcfcaaf625

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a>