

WQB A/24

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

| | |
|------------|--|
| Version | W-Series, Cross-connector, For the terminals, Number of poles: 24 |
| Order No. | 1579000000 |
| Type | WQB A/24 |
| GTIN (EAN) | 4008 190134211 |
| Qty. | 20 pc(s). |

Creation date February 27, 2023 4:10:50 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

WQB A/24

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|-----------|-----------------|------------|
| Depth | 2.5 mm | Depth (inches) | 0.098 inch |
| Height | 23.5 mm | Height (inches) | 0.925 inch |
| Width | 123.22 mm | Width (inches) | 4.851 inch |
| Net weight | 7.18 g | | |

Temperatures

| | | | |
|---------------------|----------------|----------------------------------|-------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., max. | 70 °C |
|---------------------|----------------|----------------------------------|-------|

Material data

| | | | |
|----------|---------------|--------|-------|
| Material | tinned copper | Colour | black |
|----------|---------------|--------|-------|

System specifications

| | |
|---------|-------------------|
| Version | For the terminals |
|---------|-------------------|

Additional technical data

| | | | |
|--------------------------|-----------------|---------------------|--|
| Explosion-tested version | No | Installation advice | Feed-through (bushing), Direct mounting |
| Type of fixing | when screwed in | | |

Cross-connector

| | | | |
|-------------------------------------|-----------------|---------------------------|------|
| Number of cross-connected terminals | 24 | Rated current, multi-pole | 24 A |
| Type | Cross-connector | | |

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 5.1 mm |
|-----------------|--------|

General

| | | | |
|---------------------|--|-----------------|----|
| Installation advice | Feed-through (bushing), Direct mounting | Number of poles | 24 |
|---------------------|--|-----------------|----|

Rating data

| | |
|---------------|-----|
| Rated voltage | 800 |
|---------------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000489 | ETIM 7.0 | EC000489 |
| ETIM 8.0 | EC000489 | ECLASS 9.0 | 27-14-11-40 |
| ECLASS 9.1 | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

WQB A/24

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – 18599_WQB_A-24_DXF.dxf](#)

[CAD data – STEP](#)

Engineering Data

[WSCAD_Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)