


**WQB B/24**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**



WQB B/24 157906



**General ordering data**

Version	W-Series, Cross-connector, For the terminals, Number of poles: 24
Order No.	<a href="#">1579060000</a>
Type	WQB B/24
GTIN (EAN)	4008190188597
Qty.	20 pc(s).

Creation date March 1, 2023 2:31:54 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

## WQB B/24

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	2.5 mm	Depth (inches)	0.098 inch
Height	23.5 mm	Height (inches)	0.925 inch
Width	123.22 mm	Width (inches)	4.851 inch
Net weight	8.13 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., max.	70 °C
---------------------	----------------	----------------------------------	-------

## Material data

Material	tinned copper	Colour	black
----------	---------------	--------	-------

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

## Cross-connector

Number of cross-connected terminals	24	Rated current, multi-pole	24 A
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

## General

Installation advice	Direct mounting	Number of poles	24
---------------------	-----------------	-----------------	----

## Rating data

Rated voltage	800
---------------	-----

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

## Approvals

Approvals



ROHS	Conform
------	---------

Creation date March 1, 2023 2:31:54 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

**WQB B/24**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Downloads**

---

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – 18599_WQB_B-24_DXF.dxf</a> <a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

---