

KLBUE 10-20

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image



Shielding and earthing

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

| | |
|------------|-------------------------------------|
| Version | Clamping yoke, Clamping yoke, Steel |
| Order No. | 1600490000 |
| Type | KLBUE 10-20 |
| GTIN (EAN) | 4008190151874 |
| Qty. | 10 Stück |

KLBUE 10-20

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Depth | 40 mm | Depth (inches) | 1.575 inch |
| Height | 26 mm | Height (inches) | 1.024 inch |
| Width | 24 mm | Width (inches) | 0.945 inch |
| Net weight | 29.848 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Material data

| | | | |
|----------|-------|--------|--------|
| Material | Steel | Colour | silver |
|----------|-------|--------|--------|

System specifications

| | |
|---------|-------------------------|
| Version | For a shield connection |
|---------|-------------------------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|--------|
| Explosion-tested version | Yes | Installation advice | Busbar |
| Type of fixing | Snap-on | | |

Conductors for clamping (rated connection)

| | | | |
|----------------------|-------|----------------------|-------|
| Cable diameter, max. | 20 mm | Cable diameter, min. | 10 mm |
|----------------------|-------|----------------------|-------|

Dimensions

| | |
|-----------------|-------|
| Pitch in mm (P) | 25 mm |
|-----------------|-------|

General

| | |
|---------------------|--------|
| Installation advice | Busbar |
|---------------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002020 | ETIM 7.0 | EC002020 |
| ETIM 8.0 | EC002020 | ECLASS 9.0 | 27-14-11-50 |
| ECLASS 9.1 | 27-14-11-50 | ECLASS 10.0 | 27-14-11-50 |
| ECLASS 11.0 | 27-14-11-50 | ECLASS 12.0 | 27-14-11-50 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

KLBUE 10-20

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Downloads

| | | |
|---|--|--|
| Approval/Certificate/Document of Conformity | Attestation of Conformity EAC certificate | www.weidmueller.com |
| Engineering Data | CAD data – STEP | |
| Engineering Data | WSCAD, EPLAN | |
| User Documentation | Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks | |
| Catalogues | Catalogues in PDF-format | |
| Brochures | | |