

WO 127/25 TP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Self-adhesive polyester labels which are suitable for A4 office laser printer.

General ordering data

Version	WriteOn, Conductor and cable markers, 8 - 32.3 mm, 25 x 127 mm, white
Order No.	1609770000
Type	WO 127/25 TP
GTIN (EAN)	4008190085810
Qty.	1 Stück

Erstellungs-Datum May 16, 2023 4:11:19 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

WO 127/25 TP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	25 mm	Height (inches)	0.984 inch
Width	127 mm	Width (inches)	5 inch
Net weight	33 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Material	Vinyl film	Material colour according to resistance code	9
Operating temperature range	-40...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Type of printing	neutral
UL 94 flammability rating	V-0	Version	Self-adhesive
Width	127 mm		

Conductor and cable markers

Conductor O.D.	8 - 32.3 mm	Conductor O.D., max.	32.3 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	150 mm ²
Conductor cross-section, min.	70 mm ²	Cross-section for connected wire	70 - 150 mm ²
Halogen	Yes	Text field height	25.4 mm
Text field width	25.4 mm		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, Zuken E3.S, EPLAN
Catalogues	Catalogues in PDF-format