

HDC 06B TOLU 1PG13G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 13.5
Order No.	1670500000
Type	HDC 06B TOLU 1PG13G
GTIN (EAN)	4008190431587
Qty.	1 pc(s).

HDC 06B TOLU 1PG13G

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	52 mm	Height (inches)	2.047 inch
Width	43 mm	Width (inches)	1.693 inch
Net weight	120 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Dimensions

Cable entry	w. thread	Height of housing B	52 mm
Total length housing	60 mm	Width housing C	43 mm

General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish		Powder coating	Tightening torque

Version

BG	3	Cable entry	w. thread
Clamp version	End-locking clamp	Colour (RAL)	RAL 7035
Design	Standard	Design of housing	Cable entry from top, Plug housing
Design of locking system		End-locking clamp, lower side	Internal thread
Number of cable entry on top	1	Number of cable entry sideways	0
Size	3	Size of cable entries	PG 13.5
Suitable for ModuPlug®	No	Tightening torque	1.2 Nm
Top part/bottom part/lid	upper part	Type	Plug

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant
Substance	Transmission oil
Chemical resistance	Resistant

Creation date February 28, 2023 3:58:33 PM CET

HDC 06B TOLU 1PG13G**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	d447edfa-0214-4f34-b5ba-82eae491b46a
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@4e73821f de.myview.objectmodel.impl.BlockImpl@67564e9f de.myview.objectmodel.impl.BlockImpl@130f3d3 de.myview.objectmodel.impl.BlockImpl@523a5089 de.myview.objectmodel.impl.BlockImpl@8b43ab de.myview.objectmodel.impl.BlockImpl@55fcc793 de.myview.objectmodel.impl.BlockImpl@53541894 de.myview.objectmodel.impl.BlockImpl@536aa46f de.myview.objectmodel.impl.BlockImpl@92623b2 de.myview.objectmodel.impl.BlockImpl@3ad5ad5a de.myview.objectmodel.impl.BlockImpl@4936922c de.myview.objectmodel.impl.BlockImpl@4f791eb9 de.myview.objectmodel.impl.BlockImpl@77fa8f57

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Technical Documentation	1670500000 HDC_06B_TOLU_1PG13G_STP_Blatt_1.pdf
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Creation date February 28, 2023 3:58:33 PM CET

Catalogue status 18.02.2023 / We reserve the right to make technical changes.

3

Data sheet

HDC 06B TOLU 1PG13G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

