

LM MT300 60/36 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

| | |
|------------|---|
| Version | LaserMark, Device markers, 36 x 60 mm, silver |
| Order No. | 1686430001 |
| Type | LM MT300 60/36 SI |
| GTIN (EAN) | 4008 190494 124 |
| Qty. | 10 Stück |

Erstellungs-Datum May 16, 2023 4:19:41 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

LM MT300 60/36 SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.08 mm | Depth (inches) | 0.003 inch |
| Height | 36 mm | Height (inches) | 1.417 inch |
| Width | 60 mm | Width (inches) | 2.362 inch |
| Net weight | 11.6 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|---------------------|-----------------------------------|-----------------------------------|
| Adhesive | Acrylate adhesive | Approval acc. to UL 969 | Yes |
| Colour | silver | Halogen | No |
| Material | Polyester, PVC-free | Number of markers per combination | 1 Label sheet = 21 Device markers |
| Number per sheet | 21 | Operating temperature range | -40...150 °C |
| Operating temperature range, max. | 150 °C | Operating temperature range, min. | -40 °C |
| Printing method | Laser print | UL 94 flammability rating | HB |
| Version | Self-adhesive | Width | 60 mm |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |

LM MT300 60/36 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

