

STGH ZRV1.5/PE GN**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Our plug housings provides the possibility of individual configurations of plugs. Crimp contacts on the wires are used as plug contact for a safe connection to the terminal block.

General ordering data

Version	Z-series, Plug housing, Rated cross-section: Direct mounting
Order No.	1698201001
Type	STGH ZRV1.5/PE GN
GTIN (EAN)	4008190891442
Qty.	50 pc(s).

STGH ZRV1.5/PE GN

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 1.1 g

Temperatures

Storage temperature -25 °C...55 °C

Continuous operating temp., min. -50

Continuous operating temp., max. 120

Material data

Material Wemid

UL 94 flammability rating

V-0

Additional technical data

Installation advice Direct mounting

Dimensions

TS 32 offset 34.5 mm

TS 35 offset 34.5 mm

General

Installation advice Direct mounting

Classifications

ETIM 6.0 EC002848

ETIM 7.0 EC002848

ETIM 8.0 EC002848

ECLASS 9.0 27-14-11-92

ECLASS 9.1 27-14-11-92

ECLASS 10.0 27-14-11-92

ECLASS 11.0 27-14-11-92

ECLASS 12.0 27-14-11-92

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)