

SCT 4.6/127 C

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 127 mm, Stainless steel 1.4301, 445 N
Order No.	1699800000
Type	SCT 4.6/127 C
GTIN (EAN)	4008 19089224 1
Qty.	100 Stück
Delivery status	This article will no longer be available in the future.
Available until	2022-10-31
Alternative product	2791380000

Erstellungs-Datum May 30, 2023 2:34:01 PM CEST

SCT 4.6/127 C

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.25 mm	Depth (inches)	0.01 inch
Height	127 mm	Height (inches)	5 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	1.6 g		

Temperatures

Operating temperature range	-80...538 °C	Operating temperature, min.	-80 °C
Operating temperature, max.	538 °C		

Installation materials

Cable diameter, max.	25 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4301
Operating temperature range, max.	538 °C	Operating temperature range, min.	-80 °C
Tensile strength	445 N	Tensile strength (Pound-force)	100 lbf
UV-resistant	No		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Drawing

