

SCT 4.6/838

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Similar to illustration

Weidmüller stainless steel Series contains a comprehensive assortment of stainless steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- stainless steel AISI 316,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

General ordering data

Version	Cable ties, 4.6 x 838 mm, Stainless steel 1.4301, 445 N
Order No.	1699940000
Type	SCT 4.6/838
GTIN (EAN)	4008 190892388
Qty.	100 Stück
Delivery status	This article will no longer be available in the future.
Available until	2022-06-30
Alternative product	2791440000

Erstellungs-Datum May 30, 2023 2:34:55 PM CEST

SCT 4.6/838

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	1.2 mm	Depth (inches)	0.047 inch
Height	838 mm	Height (inches)	32.992 inch
Width	4.6 mm	Width (inches)	0.181 inch
Net weight	8 g		

Temperatures

Operating temperature range	-80...538 °C	Operating temperature, min.	-80 °C
Operating temperature, max.	538 °C		

Installation materials

Cable diameter, max.	254 mm	For re-opening	No
Halogen	No	Material	Stainless steel 1.4301
Operating temperature range, max.	538 °C	Operating temperature range, min.	-80 °C
Tensile strength	445 N	Tensile strength (Pound-force)	100 lbf
UV-resistant	No		

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

SCT 4.6/838

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Drawing

