

MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Device markers, Device markers, 100 x 100 mm, yellow
Order No.	1700550001
Type	MARKO-C.100X100X100 B/DR
GTIN (EAN)	4008 190896218
Qty.	10 Stück

Erstellungs-Datum May 16, 2023 4:27:44 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.05 mm	Depth (inches)	0.002 inch
Height	100 mm	Height (inches)	3.937 inch
Width	100 mm	Width (inches)	3.937 inch
Net weight	5.8 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Permanent acrylic copolymer	Colour	yellow
Colour of printing	black	Material	Acrylic-coated fibre webbing
Material colour according to resistance code	4	Number of markers per combination	1 Label sheet = 3 Device markers
Operating temperature range	-29...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-29 °C	Printed characters	Symbols
Printing	Lightning flash in triangle	Version	Self-adhesive
Width	100 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Datenblatt

MARKO-C.100X100X100 B/DR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

