

**KLBU 4-13.5 SC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Product image**



Similar to illustration

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

**General ordering data**

Version	Clamping yoke, Clamping yoke, Steel
Order No.	<a href="#">1712311001</a>
Type	KLBU 4-13.5 SC
GTIN (EAN)	4032248032358
Qty.	10 Stück

Erstellungs-Datum May 30, 2023 2:35:04 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## KLBUE 4-13.5 SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	31.45 mm	Depth (inches)	1.238 inch
Height	22 mm	Height (inches)	0.866 inch
Width	20.1 mm	Width (inches)	0.791 inch
Mounting dimension - width	18.9 mm	Net weight	17.3 g

### Temperatures

Storage temperature -25 °C...55 °C

### Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

### System specifications

Version For a shield connection

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on	Type of mounting	Screw

### Conductors for clamping (rated connection)

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
----------------------	---------	----------------------	------

### Dimensions

Length of thread	5.3 mm	Pitch in mm (P)	20 mm
------------------	--------	-----------------	-------

### General

Installation advice Direct mounting

### Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

### Approvals

Approvals



ROHS Conform

## KLBUE 4-13.5 SC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	