

**KLBU 10-20 SC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

**General ordering data**

Version	Clamping yoke, Clamping yoke, Steel
Order No.	<a href="#">1712321001</a>
Type	KLBU 10-20 SC
GTIN (EAN)	403224803234 1
Qty.	10 Stück

## KLBUE 10-20 SC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	40 mm	Depth (inches)	1.575 inch
Height	26 mm	Height (inches)	1.024 inch
Width	23.6 mm	Width (inches)	0.929 inch
Mounting dimension - width	22.1 mm	Net weight	31.948 g

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

### System specifications

Version	For a shield connection
---------	-------------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on	Type of mounting	Screw

### Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

### Dimensions

Length of thread	5.3 mm	Pitch in mm (P)	30 mm
------------------	--------	-----------------	-------

### General

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

### Approvals

Approvals



ROHS	Conform
------	---------

## KLBUE 10-20 SC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EAC certificate</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	