

WSM 10 Q

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

WSM small plates

- Completely rust-free and acid-resistant
- Embossed characters are still legible when painted
- Also available with custom printing, embossed on a carrier
- Contents of the WSM Service Box, 40 each of: 0-9, A-Ö, +, -, x, /, :, .., ~, =, ü, Earth, Neutral. 200 steel cable ties (200 mm). 30 stainless steel carriers, 48 mm and 60 mm; 20 steel carriers, 84 mm, and 10 steel carriers, 108 mm and 288 mm

General ordering data

Version	Stainless steel markers, Conductor and cable markers, 5.5 x 9.9 mm, silver
Order No.	1712501669
Type	WSM 10 Q
GTIN (EAN)	4008 190947446
Qty.	200 Stück

Erstellungs-Datum May 16, 2023 4:33:58 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

WSM 10 Q

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.012 inch
Height	5.5 mm	Height (inches)	0.217 inch
Width	9.9 mm	Width (inches)	0.39 inch
Net weight	0.12 g		

Temperatures

Operating temperature range	500 °C
-----------------------------	--------

General data

Colour	silver	Halogen	No
Material	Stainless steel 1.4404	Number of markers per combination	1 Component part = Conductor and cable markers
Operating temperature range	500 °C	Operating temperature range, max.	500 °C
Orientation of print	horizontal	Printed characters	Upper-case letters
Printing	Q	Type of printing	Standard
Width	9.9 mm		

Conductor and cable markers

Conductor cross-section, max.	500 mm ²	Conductor cross-section, min.	16 mm ²
Cross-section for connected wire	16 - 500 mm ²	Halogen	No

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ECLASS 9.0	27-40-04-01
ECLASS 9.1	27-40-04-01	ECLASS 10.0	27-40-04-01
ECLASS 11.0	27-28-11-02	ECLASS 12.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format