

**ZQV 2.5N/5 RT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	W-Series, Cross-connector, For the terminals, Number of poles: 5
Order No.	<a href="#">1717930000</a>
Type	ZQV 2.5N/5 RT
GTIN (EAN)	4008 190349370
Qty.	20 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2021-12-31
Alternative product	<a href="#">2108710000</a>

Creation date February 20, 2023 11:02:55 AM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

## ZQV 2.5N/5 RT

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	23 mm	Depth (inches)	0.906 inch
Height	24.2 mm	Height (inches)	0.953 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	2.5 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

### Material data

Material	Wemid	Colour	red
UL 94 flammability rating	V-0		

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

### Cross-connector

Number of cross-connected terminals	5	Rated current, multi-pole	24 A
Type	Cross-connector		

### Dimensions

Pitch in mm (P)	5.1 mm
-----------------	--------

### General

Installation advice	Direct mounting	Number of poles	5
---------------------	-----------------	-----------------	---

### Rating data

Rated current	24 A
---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

### Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**ZQV 2.5N/5 RT**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks  
BPZL ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures