

CB 160/4,5 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 4.5 x 160 mm, Polyamide 66, 220 N
Order No.	1723560000
Type	CB 160/4,5 BK
GTIN (EAN)	4008 19036626 1
Qty.	100 Stück

Erstellungs-Datum May 30, 2023 2:50:33 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CB 160/4,5 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	1.3 mm	Depth (inches)	0.051 inch
Height	160 mm	Height (inches)	6.299 inch
Width	4.5 mm	Width (inches)	0.177 inch
Net weight	1.03 g		

Temperatures

Operating temperature range	-40...85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

Installation materials

Bundle diameter, max.	38 mm	Bundle diameter, min.	2.5 mm
Cable diameter, max.	40 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Downloads

Approval/Certificate/Document of Conformity	DE PI830000 160627 001
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Datenblatt

CB 160/4,5 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

