

**EA-RING MS/M 50****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	EA (earthing rings), Earthing ring, Miscellaneous, M 50, Brass, nickel-plated
Order No.	<a href="#">1736530000</a>
Type	EA-RING MS/M 50
GTIN (EAN)	4008 190963644
Qty.	10 Stück

Erstellungs-Datum May 30, 2023 2:55:53 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## EA-RING MS/M 50

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Height	111.5 mm	Height (inches)	4.39 inch
Length	111.5 mm	Length (inches)	4.39 inch
Net weight	38 g		

### Certificate numbers cable gland

Identification	Ex e II, II 2 GD, EEx d II
----------------	----------------------------

### General information

Cable glands	M 50	External thread	M 50
Gap, internal dimension B	58 mm	Inside diameter D2	13.5 mm
Material	Brass, nickel-plated	O.D.	67 mm
Thickness	1.5 mm	Width, outer dimension C	40 mm

### Classifications

ETIM 6.0	EC002317	ETIM 7.0	EC002317
ETIM 8.0	EC002317	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-90	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-07

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## EA-RING MS/M 50

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Zeichnungen

