

SKMU M16 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS (brass locknut), Locknut, M 16, 2.8 mm, Brass, nickel-plated
Order No.	1736990000
Type	SKMU M16 MS
GTIN (EAN)	4008 190956462
Qty.	100 Stück

Erstellungs-Datum May 30, 2023 2:57:26 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

SKMU M16 MS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1.43 g

General information

AF size 1	19 mm	Cable glands	M 16
External thread	M 16	Halogen	No
Internal thread	M 16	Length of thread	2.8 mm
Material	Brass, nickel-plated	O.D.	20.79 mm
Pitch of thread	1.5 mm	Thickness	2.8 mm

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ECLASS 9.0	27-14-44-24
ECLASS 9.1	27-14-44-24	ECLASS 10.0	27-14-44-24
ECLASS 11.0	27-14-44-24	ECLASS 12.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

Approvals

ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format
Brochures	

Datenblatt

SKMU M16 MS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

