

**ZQV 4N/10 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	W-Series, Cross-connector, 32 A
Order No.	<a href="#">1758260000</a>
Type	ZQV 4N/ 10 GE
GTIN (EAN)	4032248169764
Qty.	20 pc(s).
Delivery status	<b>This article will no longer be available in the future.</b>
Available until	2021-12-31
Alternative product	<a href="#">1528090000</a>

Creation date February 15, 2023 4:49:25 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

## ZQV 4N/10 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	25.7 mm	Depth (inches)	1.012 inch
Height	59.7 mm	Height (inches)	2.35 inch
Width	2.8 mm	Width (inches)	0.11 inch
Net weight	6.95 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

## Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

## Cross-connector

Number of cross-connected terminals	10	Rated current, 2-pole	32 A
Rated current, multi-pole	32 A	Type	Cross-connector

## Dimensions

Pitch in mm (P)	6.1 mm
-----------------	--------

## General

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

## Rating data

Rated current	32 A
---------------	------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

## Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**ZQV 4N/10 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Approvals**

Approvals



ROHS

Conform

**Downloads**

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[WSCAD, Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks  
BPZL ZQV 2.5](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures