

**BS 35II KLBUE2X3-8/2X2-6****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the TS 35 DIN rail. The shield is diverted from the shield clamping saddles via the mounting foot to the TS 35 mounting rail and thus to PE (ground).

**General ordering data**

Version	Clamping yoke, Set of fixings, Steel
Order No.	<a href="#">1768020000</a>
Type	BS 35II KLBUE2X3-8/2X2-6
GTIN (EAN)	4032248109296
Qty.	10 pc(s).

**BS 35II KLBUE2X3-8/2X2-6**

Weidmüller Interfaces GmbH &amp; Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	36.5 mm	Depth (inches)	1.437 inch
Height	35 mm	Height (inches)	1.378 inch
Diameter	3 mm	Net weight	72 g

**Temperatures**

Storage temperature -25 °C...55 °C

**Material data**

Material Steel Colour silver

**System specifications**

Version Clamping yoke Rail TS 35

**Additional technical data**Explosion-tested version Yes Installation advice Direct mounting  
Type of fixing when screwed in**Conductors for clamping (rated connection)**

Cable diameter, max. 8 Cable diameter, min. 3

**Dimensions**

Diameter 3 mm TS 35 offset 26.5 mm

**General**

Installation advice Direct mounting Rail TS 35

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

**Approvals**

ROHS Conform

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	