


**BS 35II KLBÜ2X2-6/2X2-6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the TS 35 DIN rail. The shield is diverted from the shield clamping saddles via the mounting foot to the TS 35 mounting rail and thus to PE (ground).

**General ordering data**

Version	Clamping yoke, Set of fixings
Order No.	<a href="#">1771990000</a>
Type	BS 35II KLBÜ2X2-6/2X2-6
GTIN (EAN)	4032248148714
Qty.	10 pc(s).

## BS 35II KLBÜ2X2-6/2X2-6

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Dimensions and weights

Depth	36.5 mm	Depth (inches)	1.437 inch
Height	35 mm	Height (inches)	1.378 inch
Net weight	61.4 g		

### Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

### Material data

Colour	silver
--------	--------

### System specifications

Version	Clamping yoke
---------	---------------

### Additional technical data

Explosion-tested version	No
--------------------------	----

### Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>