

**SKMU EMV M16****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Version	SKMU MS EMV (brass locknut - EMC), Locknut, M 16, 3.6 mm, Brass, nickel-plated
Order No.	<a href="#">1777620000</a>
Type	SKMU EMV M16
GTIN (EAN)	4032248157891
Qty.	100 Stück

Erstellungs-Datum May 30, 2023 3:10:08 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## SKMU EMV M16

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 1.85 g

### General information

AF size 1	19 mm	Cable glands	M 16
External thread	M 16	Halogen	No
Internal thread	M 16	Length of thread	3.6 mm
Material	Brass, nickel-plated	O.D.	20.79 mm
Pitch of thread	1.5 mm		

### Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ECLASS 9.0	27-14-44-24
ECLASS 9.1	27-14-44-24	ECLASS 10.0	27-14-44-24
ECLASS 11.0	27-14-44-24	ECLASS 12.0	27-14-08-05

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">WSCAD, EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

SKMU EMV M16

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Zeichnungen

